

Rapid Deployment Solutions for Temporary Healthcare Facility Networks


Life Is On




We are here to help you deploy network and IT equipment into temporary screening, triage, and ICU spaces with speed, security, and secure power.




6U MicroDC
Based on AR106V rack

- 


Compact, Portable and Re-Deployable Rack System

 - Wall mount or deploy with available casters
 - Filtered door to protect equipment in harsher environments
- 

Security to Protect EHRs (HIPAA)

 - Lockable doors
 - Attach Netbotz video camera
- 

Rapidly Deployable

 - Pre-Integrated in the factory
- 

Secure Power and Cloud Connectivity

 - UPS protected for potentially unstable temporary spaces
 - Customers who want to become pro-active with management



Other Rack and UPS Options

NetShelter SX
Standard Compact
IT Rack



NetShelter CX
Office Furniture Style
Soundproof Rack



SmartBunker FX
Ruggedized Climate
Controlled Rack



Smart-UPS
Lithium Ion



Smart-UPS UPS
Traditional Rack or Tower



Additional Offers

Surge Suppressors for Safe Power Distribution
(not UL60601 compliant)



UPSs for other important availability needs
(not UL60601 compliant)



Remote Services to Ensure Visibility and Availability

