

Honeywell

N95 Alternative Respiratory Selection Guide

(Based on production capacity)

Half-Masks

550030*S,M,L

770030*S,M,L



Full-Face

54001S (S)
54001 (M/L)

RU65001*
(S,M,L)

760008AS (S)
760008A (M/L)



Filters

7580P100

(P100)

75FFP100



Honeywell

PAPR Selection

Biological & Mild Cleaning*

(P100 Only)



Hood Options

PA101

PA111



PA101

PA111

*PAPR can also be used with any Honeywell half or full-face respirator

Unit: PA701HED

Choose either:

Hood Breathing Tube: PA031

Tight-fitting Breathing Tube: PA034



Unit: PR501*

*mask size:


S,M,L



Filter

PA7HE

(P100)



Filter

108000-H5

(P100)

*PAPR utilizes the Honeywell RU6500 full-face respirator