



Health Care Facility

Sales Guide



Public & Administration Areas

Heavy Duty Hospital Grade Receptacles

- 15 & 20 Amp/125 Volt
- Isolated Ground & Illuminated Versions Available
- UL/Fed. Spec./CSA/NOM



Decora® Hospital Grade Tamper-Resistant & Non-Tamper-Resistant Receptacles

- 15 & 20 Amp/125 Volt
- Indicator Light and Audible Alarm
- Conform to UL 1449



Hospital Grade 4-in-1 Receptacles

- 15 & 20 Amp/125 Volt NEMA Configurations
- Isolated Ground and Non-Isolated Ground



Hospital Grade USB Charger/Tamper-Resistant Receptacles

- 15 & 20 Amp/125 Volt
- USB Charger/Tamper-Resistant Receptacle & 4-Port USB Charger Versions Available
- 3.6A Charging Capacity for Duplex Receptacle Versions
- 4.2A Charging Capacity for 4-Port USB Version
- cCSAus/NOM



Hospital Grade AFCI Receptacles

- 15 & 20 Amp/125 Volt
- LED Indicator Light
- Tamper-Resistant
- Self-Grounding
- UL/ CSA/NOM/Fed.Spec.



AC Toggle and Decora Plus Switches

- 20A-120/277 VAC
- Single Pole, Double Pole, 3-Way
- Pilot Light, Illuminated and Antimicrobial Treated versions
- UL/Fed.Spec./CSA



Lev-Lok® Toggle Switches

- 15 & 20 Amp/120 & 240 Volt
- Standard, Tamper-Resistant and Illuminated versions available
- Color-coded covers: 15 Amp-Blue, 20 Amp-Red for easy circuit identification



Key Locking Switches

- Single Pole, Double Pole, 3-Way, 4-Way
- Replacement keys available



Tamper-Resistant Toggle Switches

- 20A-120/277V
- 1HP-120V 2HP-240V-277V
- UL/Fed.Spec./CSA/NOM



Hospital Grade Python®

- 15 & 20A/125 & 250V
- NEMA and Non-NEMA Configurations
- Patented interlock design for secure installation
- Clear thermoplastic terminal cover



Metallic Wallplates

- Available in Type 302 and 430 Stainless Steel, Aluminum, Chrome and Brass
- Expansive selection of single- and multi-gang configurations
- Antimicrobial treated versions helps resist development of mold, mildew, fungi and other odor-causing bacteria



Surge Protective Panels

- 120/208, 277/480 3-Phase Voltages
- Compliant with 2017 NEC requirement for emergency power systems
- Limited Lifetime Warranty



Biomedical Operations & Patient Care

Extra Heavy Duty Hospital Grade Receptacles

- 15 & 20 Amp/125 & 250 Volt
- 0.050" Nickel-Plated 1-piece Brass Strap
- Triple-wipe 0.040" high-performance brass alloy contacts
- Tamper-Resistant, Power Indication & MRI Versions Available
- UL/Fed. Spec./CSA/NOM



Decora Plus™ Extra Heavy Duty Hospital Grade Receptacles

- 15 & 20 Amp/125 Volt
- Back & Side Wired
- Tamper-Resistant, Isolated Ground & Power Indication Versions Available
- UL/CSA/NOM



Hospital Grade 4-in-1 Receptacles

- 15 & 20 Amp/125 Volt
- Steel Strap
- Isolated Ground Versions Available
- UL/ CSA/NOM



Biomedical Operations/Patient Care

Lev-Lok® Hospital Grade Receptacles

- 15 & 20 Amp/125 Volt
- Standard, Decora, Illuminated or Power Indication
- GFCI, Tamper-Resistant, MRI & Isolated Ground versions available



Lev-Lok® Decora Plus Hospital Grade Receptacles

- 15 & 20 Amp/125 Volt
- Standard, Illuminated or Power Indication
- Tamper-Resistant and Surge Protective versions available



Antimicrobial Treated Devices

- 20A-120/277 VAC
- Available in Toggle, Decora Plus™, and Lev-Lok® switches and stainless steel toggle and Decora® wallplates
- Made with an E.P.A. registered additive
- Helps resist development of mold, mildew, fungi and other odor-causing bacteria
- Certified by NSF International to meet sanitation requirements for use in food handling and processing environments



Special Purpose Wallplates Pre-marked with "EMERGENCY" for Easy Identification

- Available in either nylon or stainless steel single-and two-gang configurations; Standard or Midway sizes
- Nylon wallplates are red in color with "EMERGENCY" lettering in black or white
- Stainless steel wallplates have "EMERGENCY" lettering in high visibility red



Medical Grade Power Strips

- 15 & 20 Amp/125 Volt
- Available with 2, 4 or 6 hospital grade outlets
- 7 or 15 feet cord length
- UL 60601-1, UL 1363A, and UL 60950-1 compliant to meet all major safety regulations required for health care facilities
- Also available in non-surge protective configurations



Hospital Grade Plugs and Connectors

- 15 & 20 Amp/125 Volt
- NEMA and Non-NEMA Configurations
- 2-P 3-W



Maintenance, Parking & Outdoor Areas

Black & White® Industrial Grade

- 15, 20 & 30 Amp
- 125V thru 600V
- 2-P 2-W thru 4-P 5-W
- NEMA and Non-NEMA Configurations
- UL/Fed.Spec./CSA/NOM



Maintenance, Parking & Outdoor Areas

Safety Disconnect Switches

- 30A, 60A, and 100A, Fused & Non-Fused in Non-Metallic Enclosures
- 30A, 60A, 80A and 100A, Non-Fused in Stainless Steel Enclosures
- IP69K for high pressure, high temperature washdown
- NSF Certified for hygiene requirements
- IP67, IP65, NEMA 3R, 4X, 12K



Weatherproof Device Covers & Boxes

- Available in 1- and 2-gang configurations
- Complies with the NEC® (2017) Section 406.9(A) for weatherproof enclosures in damp locations
- Vertical or Horizontal Mounting



Evr-Green® Network Charging Stations

- Two Level 2 charging ports each supplying up to 7.2kW (208/240VAC @30A)
- SAE J1772™ Compatible
- Self-retracting cord management system



Evr-Green® Non-Network Charging Stations

- 20, 30, or 40 Amp
- SAE J1772™ Compatible



Kitchen, Restrooms & Hydrotherapy Areas

Hospital Grade Self-Test GFCI Receptacles

- 15 & 20 Amp/125 Volt
- PBT Cover
- NAFTA Compliant, Tamper-Resistant & Weather-Resistant Versions Available
- UL/CSA/NOM/Fed. Spec. Rated



Wetguard® Straight Blade and Locking Devices

- 15, 20 and 30 Amp
- 125V thru 600V
- 2-P 2-W thru 4-P 5-W
- NEMA and Non-NEMA Configurations



Wetguard® Watertight Switch Cover

- IEC IP66 and NEMA 4X watertight ratings
- For use with any standard single pole toggle switch 15A to 30A
- Lockout handle meets OSHA safety regulations



Lighting and Energy Management

Provolt™ Room Controller (PRC) and App

- 120/277V
- Self-contained device for occupancy sensing, 0-10V dimming, daylight harvesting, partial-ON, partial-OFF, plug load control and demand response
- Configuration and control via the Provolt™ Bluetooth® mobile app
- Install with Provolt™ Keypad for manual control - 1, 2, or 4 button
- 1- or 2-zone control
- UL/cUL, CE, NOM, RoHS, NEMA



Ceiling-Mount Multi-Technology Occupancy Sensors*

- Supports 24VAC/DC power supplies
- Coverage Range: 500-2000 Sq. Ft.
- CUL/US, FCC and NOM Certified

*Meets requirements for ASHRAE 90.1, IECC and Title 24



IllumaTech® Dimmers

- 120VAC, 60 Hz, Neutral wire required
- 1000W Incandescent
- 150W LED/CFL
- 1000VA Magnetic Low Voltage
- 1000VA Fluorescent Ballast
- 1200VA 0-10V Power Supplies



SureSlide® Dimmers

- Integrated linear full range slide control for easy, precise operation.
- Preset versions feature a separate on/off switch that preserves the selected brightness or fan speed setting
- Dimmers and fan speed controls feature elegant designer styling that coordinates perfectly with Leviton's extensive line of Decora® wiring devices and wallplates.
- Preset versions provide single pole or 3-way lighting control when used with a 3-way switch Illuminated versions feature optional use locator light



Multi-Technology Wall or Corner Mount Occupancy Sensors

- Supports 24VAC/DC power supplies
- Coverage: 1200 Sq. Ft.
- Adjustable swivel neck rotates 80° vertically and 60° horizontally
- CUL/US Certified



Decora® Wall Switch Multi-Technology Occupancy Sensors*

- 120-277VAC, 50/60Hz
- LED, Incandescent/Tungsten, Fluorescent
- UL and cUL Listed, ETL and cETL Listed

*Meets requirements for ASHRAE 90.1, IECC and Title 24



Lev-Lok® Occupancy Sensors*

- Available in Passive Infrared (PIR) and Multi-Technology (Ultrasonic and PIR) versions
- 180° field-of-view provides approximately 2100 square feet of coverage suitable for small offices, conference rooms, classrooms, lounges and a variety of commercial areas

*Meets requirements for ASHRAE 90.1, IECC and Title 24



VerifEye™ Meter Kits – Indoor & Outdoor**

- 100A – 5000A, 120V - 277/480V
- Single Phase & Three Phase
- Isolated Pulse Output Standard
- NEMA 1, 4X Enclosures
- Data collection hardware and BMO 3.0 energy information software available

**Meets requirements for ASHRAE 90.1 and Title 24



Integrated Room Control (IRC) Kit

- 120/277V, 347V
- Kit includes IRC, sensor, photocell and keypad for occupancy sensing, 0-10V dimming, daylight harvesting, partial-ON, partial-OFF and demand response
- Add OPP20 for plug load control
- 2- or 3-zone control
- UL/cUL Listed



Visit our Website at:

leviton.com/healthcare



Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

© 2019 Leviton Manufacturing Co., Inc. All rights reserved.

ED-G-00123
Health Care Facility
Sales Guide_
CRESCENT_AO

